

# Mouth-actuated Tester GT-M03

## Product Introduction

### Application:

This Mouth Toy Durability Tester is suitable for the test of the safety of the Mouth-Actuated Toys, such as whistles with a ball, the sounders with a reed and other toys.

This tester will blow-off certain volume gas in a certain speed and inhale the toy, blow-off and inhale alternately for 10 times, after the test, you should test the toy and the deciduous parts whether they are findings.

### Satndards:

EN 71-1

ISO 8124-1

ASTM F963

GB 6675.2

## Dimensions

<b>External Dimension:</b>	
500*420*260 mm(L*W*H)	
<b>Package Dimension:</b>	
670*470*380 mm(L*W*H)	
<b>Gross Weight:</b>	
43KG	
<b>Net Weight:</b>	
35KG	

## Key Specifications

Model	GT-M03
Blow and suck air volume	295±10 cm <sup>3</sup>
Blow and suck frequency	1 cycle/ 5s
Test air pressure	13.8 Kpa
Testing times	10 times
Air pressure meter	Digital, Units, Kpa; The positive and negative pressure display
Dimensions (L×W×H)	27×56×39cm
Weight	≈24kg
Power supplier	AC220V 50/60HZ
Accessories	Tube gripper -3pcs

## Application Industry

All kinds of Mouth Toys can be tested on the Mouth-actuated Tester

